

General printing guidelines

T-Flex

- » Add **8mm bleed**
- » Recommended resolution 1:1 100-150 dpi
Bigger is better!
- » Graphics over 5000 mm should be presented at
a scale of 1:10 min 600 dpi
- » CMYK (ISO Coated v2)
- » Do not add bleed or crop marks (unless
indicated otherwise)
- » PDF (PDF/X-1a)
TIFF (LZW compression is recommended)
- » Rich black: C 50 M 40 Y 40 K 100
- » **Please do not use *Overprint***

File transfer options:

WeTransfer:

<https://comdecor.wetransfer.com/>

E-mail:

sales@comdecor.eu (max 7 MB)

**COM
DECOR**